


- NOTES CONTINUED:
- SCRIBE, ENGRAVE, OR MECHANICALLY STAMP (NO INKS OR DYES) DRAWING PART NUMBER AND REVISION ON NOTED SURFACE FOLLOWED ON THE NEXT LINE BY A THREE DIGIT SERIAL NUMBER. SERIAL NUMBERS START AT 001 FOR THE FIRST ARTICLE AND PROCEED CONSECUTIVELY. USE .07" HIGH CHARACTERS. EXAMPLE: DXXXXX-VV, S/N 001. VIBRATORY TOOL MAY BE USED.
  - APPROXIMATE WEIGHT = X.XXX LB.
  - MACHINE ALL SURFACES TO REMOVE OXIDES AND MILL FINISH. USE OF ABRASIVE REMOVAL TECHNIQUES IS NOT ALLOWED. REFER TO LIGO-E0900364
  - ALL PARTS SHALL BE MANUFACTURED IN ACCORDANCE WITH LIGO SPECIFICATION E0900364.
  - ALL HELI-COIL HOLES TO BE PREPARED ACCORDING TO EMHART HELI-COIL PRODUCT CATALOG, HC2000, REV.4
  - ALL HELI-COIL INSERTS TO BE INSTALLED BY LIGO PERSONNEL. AFTER DELIVERY OF FINISHED PARTS, USE NITRONIC-60 THREADED INSERTS.



- ALL MATERIAL IS TO BE VIRGIN MATERIAL (i.e. NO WELD REPAIRS, PLUGS OR RECYCLED MATERIAL). NO REPAIRS SHALL BE MADE UNLESS APPROVED IN ADVANCE, AND IN WRITING, BY LIGO LABORATORY. REFER TO LIGO-E0900364.
- SURFACE FINISH TO BE AS-PROCESSED FROM MILL/SUPPLIER, FREE FROM SCRATCHES OR GOUGES.
- PART WILL BE PORCELAIN COATED PER LIGO SPECIFICATION E1000083 AFTER FABRICATION. THE INDICATED HOLES WILL BE MASKED PRIOR TO PORCELAIN COATING TO APPROXIMATELY 2.5-3X HOLE DIAMETER CENTERED ON BOTH SIDES OF THE HOLE.
- DIMENSIONS APPLY BEFORE PORCELAIN COATING UNLESS SPECIFIED.
- BEND RADIUS: UNLESS OTHERWISE NOTED, THE BEND RADIUS SHOULD BE THE MINIMUM REQUIRED TO FORM WITHOUT CRACKING OR REQUIRING ADDITIONAL WORK WHEN FORMING. IN PARTICULAR IF SHEET METAL IS TO BE PORCELAIN COATED, THE BEND RADIUS SHALL BE A MINIMUM OF .12" OUTSIDE RADIUS OF BEND UNLESS OTHERWISE NOTED.

NOTES 9, 10, 13 and 14 DO NOT APPLY TO THIS PART.

### CONNECTOR J1



### CONNECTOR J2



### V25B-216 CABLE ASSEMBLY CIRCUIT SUMMARY V-DB25HD F/S1-216-DB25HD F/S1

CABLE NAME	COND.- WIRE ID	DOUBLE TWISTED PAIR	LENGTH *	FROM	TO
V25B-216	16 COND. CABLE	(12 TOTAL)	216 in.	Conn. J1	Conn. J2
	SHIELD		216 in	PIN 1, SHELL	PIN 1, SHELL
	W13	TP-1	216 in	PIN 13	PIN 13
	W25		216 in	PIN 25	PIN 25
	W12	TP-2	216 in	PIN 12	PIN 12
	W24		216 in	PIN 24	PIN 24
	W11	TP-3	216 in	PIN 11	PIN 11
	W23		216 in	PIN 23	PIN 23
	W10	TP-4	216 in	PIN 10	PIN 10
	W22		216 in	PIN 22	PIN 22
	W9	TP-5	216 in	PIN 9	PIN 9
	W21		216 in	PIN 21	PIN 21
	W8	TP-6	216 in	PIN 8	PIN 8
	W20		216 in	PIN 20	PIN 20
	W7	TP-7	216 in	PIN 7	PIN 7
	W19		216 in	PIN 19	PIN 19
	W6	TP-8	216 in	PIN 6	PIN 6
	W18		216 in	PIN 18	PIN 18

PIN 14,2,15,3,16,4,17,5 N/C (NOT CONNECTED)  
 \* THE LENGTH SHOWN IN THIS LIST IS THE LENGTH OF THE CABLE BETWEEN THE TWO CONNECTORS. ADD ADDITIONAL LENGTH AS NECESSARY FOR THE INTERNAL WIRING OF THE CONNECTORS AND STRIP LENGTH.


SEE REFERENCE DCC# LIGO-D1100670

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.	LENGTH
1	TICOR # (TS0148-25C020BS1-325) OR EQUIVALENT **	DB25 FEMALE CONNECTOR (J1) FOR UHV (PLAIN PEEK)	1	
2		DB25 CONNECTOR BACKSHELL (NO EARS) FOR UHV (STAINLESS) WITH Ø0.325" I.D. PORT	1	
3	TICOR # (TS0148-25C020BS1-325F) OR EQUIVALENT **	DB25 FEMALE CONNECTOR (J2) FOR UHV (GOLD METALIZED PEEK)	1	
4		DB25 CONNECTOR BACKSHELL (WITH EARS) FOR UHV (STAINLESS) WITH Ø0.325" I.D. PORT	1	
5	COONER WIRE # CZ2205 22GA PFA INSULATED BIOMEDICAL WIRE	16 COND. (8 TW PAIR) CABLE WITH 6 COPPER BRAID (SHIELD) AND 7 PEEK OVERBRAID	1	216in *
6	CONTINENTAL PART #24x3x40BC	COPPER BRAID - CONTINENTAL CORDAGE PART #24x3x40BC	1	
7	PART # 6759	PEEK BRAID - PART #6759 MANUFACTURED WITH ZEUS 0.016" BLACK PEEK DRAWN MONOFILAMENT - SUPPLIED BY LIGO	1	
8	GLENAIR # 600-052 or BAND-IT # A10086	GLENAIR # 600-052 STANDARD BRAID CLAMP or BAND-IT PART # A10086 (0.240" WIDE) ("BAG OF 100" # A10089)	2	

\* NOTE: USE WHATEVER LENGTH IS NECESSARY FOR THE INTERNAL WIRING OF THE CONNECTORS AND STRIP LENGTH TO ACHIEVE THE CORRECT OVERALL LENGTHS.  
 \*\* NOTE: SEE THE "TICOR CONNECTOR PART NUMBER BUILDER" DCC#D1000219 FOR DETAILS ON THIS PART NUMBER.

#### NOTES: ( UNLESS OTHERWISE SPECIFIED )

- MATERIAL:
  - J1 CONNECTOR SHELL - PEEK VICTREX 450G130.
  - J2 CONNECTOR SHELL - GOLD OVER ELECTRO-LESS NICKEL SELECTIVELY METALIZED PEEK VICTREX 450G130.
  - BACKSHELLS - STAINLESS STEEL WITH VENT HOLE.
  - CONTACTS - BERYLLIUM COPPER ALLOY C17300, 0.00050 MIN. GOLD OVER NICKEL.
  - HARDWARE: STAINLESS STEEL, PASSIVATED.
  - PEEK BRAID - PEEK VICTREX GRADE TDS-450CA30 CARBON LOADED - SUPPLIED BY LIGO.
- CABLE 16 COND. 22 AWG (150/44), WITH PFA INSULATION COONER WIRE #CZ2205. 8 TWISTED PAIRS ( 4 TO 5 TWISTS PER INCH ). OVERALL 40AWG COPPER BRAID SHIELD MIN. 50% COVERAGE - SUPPLIED BY LIGO. OVERALL PEEK BRAID MIN. 50% COVERAGE. OVERALL CABLE O.D. ~ 0.260 IN.
- CONNECTORS WILL BE SUPPLIED WITH HARDWARE. SCREWS SHOULD BE THE PROPER LENGTH FOR MATING.



#### NOTES AND TOLERANCES: (UNLESS OTHERWISE SPECIFIED)

DIMENSIONS ARE IN	1. INTERPRET DRAWING PER ASME Y14.5-1994.		LIGO CALIFORNIA INSTITUTE OF TECHNOLOGY MASSACHUSETTS INSTITUTE OF TECHNOLOGY	
TOLERANCES:	2. REMOVE ALL SHARP EDGES, .005-.015, FOR MACHINED PARTS. ROUND ALL EDGES APPROXIMATELY R.02 FOR SHEET METAL PARTS.		PART NAME	
.XX ±	3. DO NOT SCALE FROM DRAWING.		CUSTOM CABLE SPECIFICATION V25B-216	
.XXX ±	4. ALL MACHINING FLUIDS MUST BE FULLY SYNTHETIC, FULLY WATER SOLUBLE AND FREE OF SULFUR, SILICONE, AND CHLORINE.		DESIGNER	R. ABBOTT
ANGULAR ± °	MATERIAL	FINISH	DRAFTER	E. BROWN
	Material <not specified>	μinch	CHECKER	
			APPROVAL	

ISC TRANSMON PICOMOTOR CABLE VACUUM FLANGE TO SEISMIC TABLE		
V-DB25HD F/S1-216-DB25HD F/S1		
STANDARD USE FOR THIS CABLE		
SUBSYSTEM	AIR/VAC	STANDARD USE
ISC & ISC(TMS)	IN-VAC	PICOMOTORS - FLANGE TO TOP

SYSTEM	LIGO	SUB-SYSTEM	ISC & ISC(TMS)	DESIGNER	R. ABBOTT	JUL/02/2012	SIZE	DWG. NO.	D	D1000223	REV.	v6
NEXT ASSY		CHECKER		APPROVAL			SCALE: 1:1	PROJECTION:			SHEET 1 OF 1	