





NOTES CONTINUED:

- 5. SCRIBE, ENGRAVE, OR MECHANICALLY STAMP (NO DYES OR INKS) A UNIQUE THREE DIGIT SERIAL NUMBER & REVISION NUMBER ON EACH PART. SERIAL NUMBERS START AT 001 FOR THE FIRST ARTICLE AND PROCEED CONSECUTIVELY. BAG AND TAG PARTS WITH THEIR DRAWING PART NUMBER, REVISION, VARIANT OR "TYPE" (IF APPLICABLE), AND QUANTITY. IF PARTS ARE TOO SMALL TO SCRIBE, BAGGING AND TAGGING ALONE IS SUFFICIENT.
EXAMPLE (PART): 001-v1
EXAMPLE (TAG): DXXXXXX-VY, TYPE-XX, QTY: TBD
- 6. APPROXIMATE WEIGHT = .06 LB [.03 KG].
- 7. ALL PARTS SHALL BE MANUFACTURED IN ACCORDANCE WITH LIGO SPECIFICATION E0900364.
- 8. ALL MATERIAL IS TO BE VIRGIN MATERIAL (i.e. NOT WELD REPAIRS OR PLUGS UNLESS APPROVED IN ADVANCE IN WRITING BY LIGO. REFER TO LIGO-E0900364.
- 9. NO REPAIRS SHALL BE MADE UNLESS APPROVED IN ADVANCE, AND IN WRITING, BY LIGO LABORATORY. IN GENERAL WELD REPAIRS AND PRESS FIT INSERT REPAIRS ARE NEVER ACCEPTABLE; THE MATERIAL SHOULD BE MADE WITH VIRGIN MATERIAL. SPECIAL CIRCUMSTANCES CAN BE REVIEWED IF / WHEN BROUGHT TO THE ATTENTION OF LIGO CONTRACTING OFFICER'S REPRESENTATIVE (COTR) THROUGH A MATERIAL REVIEW BOARD (MRB) PROCESS, REFER TO LIGO-E0900364.
- 10. MODIFY DEL-TRON RS1-2 GUIDE.
- 11. USE .005 OVERSIZE DRILL & TAP.

REV.	DATE	DCN #	DRAWING TREE #
v1	10/12/2010	E1000318	-
v2	10/29/2010	E1000602	-
-	-	-	-



2X 4-40 X ∇ .40 (EXISTING)



2X 4-40 X ∇ .40 (EXISTING)

D1001953 qLIGO TMS DEL-TRON RS1-2 FOCUS GUIDE, PART PDM REV: X-022, DRAWING PDM REV: X-017

NOTES AND TOLERANCES: (UNLESS OTHERWISE SPECIFIED)				LIGO CALIFORNIA INSTITUTE OF TECHNOLOGY MASSACHUSETTS INSTITUTE OF TECHNOLOGY		PART NAME	
DIMENSIONS ARE IN INCHES TOLERANCES: .XX \pm .01 .XXX \pm .005 ANGULAR \pm °				1. INTERPRET DRAWING PER ASME Y14.5-1994. 2. REMOVE ALL SHARP EDGES, R.02 MIN. 3. DO NOT SCALE FROM DRAWING. 4. ALL MACHINING FLUIDS MUST BE FULLY SYNTHETIC, FULLY WATER SOLUBLE AND FREE OF SULFUR, SILICONE, AND CHLORINE.		aLIGO TMS DEL-TRON-RS1-2 FOCUS GUIDE	
MATERIAL		FINISH		SYSTEM		SUB-SYSTEM	
10		N/A μ inch		LIGO		AOS	
NEXT ASSY				DESIGNER		DATE	
D1001951				K. MAILAND		07/29/2010	
APPROVAL				DRAFTER		SIZE DWG. NO.	
				M. MILLER		B	
				CHECKER		D1001953	
				APPROVAL		v2	
SCALE: 1:1				PROJECTION:		SHEET 1 OF 1	