LIGO L

LASER INTERFEROMETER GRAVITATIONAL WAVE OBSERVATORY

SPECIFICATION

E1000671 -V1

Drawing No Vers.

Sheet 1 of 2

aLIGO ISC optics: 1" and 2" 50:50 beam splitters

APPROVALS	DATE	RE V	DCN NO.	BY	CHECK	DCC	DATE
AUTHOR: L. BARSOTTI	12-08-10						
CHECKED:							
APPROVED: P. FRITSCHEL							
DCC RELEASE							

1 Description

 $1"\emptyset$ and $2"\emptyset$ 50:50 beam splitters @ 1064nm

2 Material

Corning HPFS 7980 (high purity fused silica, UV grade) Grade 0A (Low inclusion class: <0.3 mm² cross section, 0.1 mm max. size; Homogeneity < 1ppm)

3 Dimensions, Surface Roughness and Figure

E1000671-v1-01

 $1"Ø + .000/-.005" X .250" \pm .020" tk., Plano / Plano$

Wedge: 30 arc minutes \pm 5 arc minutes

Surface Roughness:

Side 1

Super polish

Surface Roughness: <1 Å RMS in CA

Surface Quality: 10-5

Side 2

Commercial Polish

Surface Roughness: <5Å RMS in CA

Surface Quality: 20-10

Surface Figure:

Side 1

Flat $< \lambda/10$ at 632.8 over central 80%

Side 2

Flat $< \lambda/4$ at 632.8 over central 80%



SPECIFICATION

E1000671 -V1

Drawing No Vers.

Sheet 2 of 2

aLIGO ISC optics: 1" and 2" 50:50 beam splitters

E1000671-v1-02

2"Ø +.000/-.005" X .375" ± .020" tk., Plano / Plano

Wedge: 30 arc minutes \pm 5 arc minutes

Surface Roughness:

Side 1

Super polish

Surface Roughness: <1Å RMS in CA

Surface Quality: 10-5

Side 2

Super Polish

Surface Roughness: <1Å RMS in CA

Surface Quality: 20-10

Surface Figure:

Side 1

Flat $< \lambda/10$ at 632.8 over central 80%

Side 2

Flat $< \lambda/5$ at 632.8 over central 80%

4 Coating

Wavelength: 1064nm Angle of incidence: 45°

Side 1

50:50 (R:T) for \mathbf{p} polarization Absolute value of (R-T) < 1%

Side 2

AR coating, R < 0.1% (best effort) for p-polarization

Arrow pointing to side 1, serial numbers and registration marks shall be scribed or etched on the barrel of the optic for in-vacuum use.

Coating vendor to provide:

- 1. Two spectrophotometer graphs of the reflectance and transmittance of the HR coatings; one covering the spectrum from $530\,\mathrm{nm}$ to $1200\,\mathrm{nm}$; the other, with increased sensitivity, showing wavelengths from $900\,\mathrm{nm}$ to $1100\,\mathrm{nm}$
- 2. Spectrophotometer graphs of the reflectance of the AR coating taken as cited above.