



H1 Handle, 1.25"

H2 Handle, 1.25"

Mouser
534-9106

H3 Ferrule, 0.25"

H4 Ferrule, 0.25"

H5 Ferrule, 0.25"

H6 Ferrule, 0.25"

Mouser
534-9121

M1 #6-32 1/4" flat

M2 #6-32 1/4" flat

M3 #6-32 1/4" flat

M4 #6-32 1/4" flat

M5 #6-32 1/4" flat

M6 #6-32 1/4" flat

McMaster-Carr
91099A205

PN1
Front Panel
LIGO
D1100693-v1

PN2
Rear Panel
LIGO
D1100694-v1

PN3
Top Panel
LIGO
D1100695-v1

E1 Standoff, 0.375"

E2 Standoff, 0.375"

Mouser
534-1902B

D1
LED Indicator
Digi-Key
350-2127-ND

PN4
Bottom Panel
LIGO
D1100695-v1

H7 #4 screw, 3/8"

H8 #4 screw, 3/8"

Mouser
534-9328

PN5
Side profile

PN6
Side profile
Frontpanel Express
Side profile 1, 150mm

PN7
Housing bracket
Frontpanel Express
Housing bracket 8 x per unit, natural anodized

PN8
Assembly kit
Frontpanel Express
Assembly kit ISP/B3.0-NI DIN 7982, nickel-plated

PN9
Screw kit
Frontpanel Express
Screw packet M3x6-965-NI DIN 965, nickel-plated

PN10
D-Sub cable, DB9

PN11
D-Sub cable, DB9

PN12
D-Sub cable, DB9

PN13
D-Sub cable, DB9

PN14
D-Sub cable, DB15

PN15
D-Sub cable, DB15

PN16
D-Sub cable, DB15

PN17
D-Sub cable, DB15

PN18
IDC socket, 10pin

PN19
IDC socket, 10pin

PN20
IDC socket, 10pin

PN21
IDC socket, 10pin

PN22
IDC socket, 16pin

PN23
IDC socket, 16pin

PN24
IDC socket, 16pin

PN25
IDC socket, 16pin

PN26
Screwlock kit

Title Controls Concentrator LSC Demodulator		
Size A	Number D1100691	Revision 1
Date: 10/4/2011	Sheet 1 of 1	
File: C:\Users\...\ConcentratorDemodLSC1.SchDoc	Drawn By: Daniel Sigg	