

LIGO HANFORD OBSERVATORY PO BOX 159 RICHLAND WA 99352 TEL: 509.372.8106 FAX: 509.372.8137

MEMORANDUM

DATE: January 14, 2022 TO: Slow controls team FROM: Daniel Sigg SUBJECT: Modifications to the Beckhoff chassis Refer to: LIGO-E2000499-v3

Due to the elimination of the end station computers the remote access chassis in the end stations can be simplified. A set of terminals is removed including the bridge terminal that was used to communicate between computers.

Change 1: Remote Access End

Drawing: D1100619-v3 Wiring diagram: E1100455-v3 Work: Combined the terminals into a single rail and remove terminals that are no longer needed Needed: 2x D1100095-v2 per end station (4 total/site)

Change 2: Remote Access Corner

Drawing: D1100618-v2 Work: Verify the position of the EL9400 terminal

The rotation stages are put on a separate rail that can be independently power cycled. As part of the A+ upgrade a picomotor controller for the PSL is added.

Change 3: PSL/IO/TCS Controls Chassis

Drawing: D1101114-v6 Wiring diagram: E1100530-v8 Work: Separate rotation stage onto separate rails, add relay for power on/off Add picomotor interface terminals for A+ Needed by rotation stage upgrade: 1x EK1122 1x EK1101

1x EL1094 1x EL2612

CALIFORNIA INSTITUTE OF TECHNOLOGY



Needed by A+ upgrade: 1x D2000017-v1 (superseded by version 2) 2x D1100419-v3 1x EL9410 1x EL3102 1x EL1014 1x EL1872 1x EL2872

Controls and readbacks for the T-SAMS and the P-SAMS are needed for A+.

Change 4: PSL/IO/TCS Controls Chassis

Drawing: D1101114-v7 Wiring diagram: E1100530-v9 Work: Add terminals for a new middle rail for the P-SAMS Add terminals to the end of the right rail for the T-SAMS Needed for the new middle rail: 1x D2000017-v2 2x D0902567-v1 1x EK1100 4x EL3104 1x EL9190 1x EL9011 Needed for the right rail upgrade: 2x D0902568-v1 1x EL9410 2x EL3104 2x EL3692 1x EL4132

CALIFORNIA INSTITUTE OF TECHNOLOGY



Additional picomotor controller interfaces are added to the corner chassis 2 for A+.

Change 5: EtherCAT Corner 2

Drawing: D1100680-v3 Wiring diagram: E1101126-v3 Work: Add 3 picomotor controller interfaces Needed by A+ upgrade: 1x D1102268-v2 1x EL9410 3x EL3102 3x EL1014 3x EL1014 3x EL1872 3x EL2872 1x D1100419-v3

The EtherCAT chassis near HAM8 may require picomotor controllers as well.

Needed by A+ upgrade: 2x D1100419-v3

Two sets of controls for the AM modulated AOM amplifiers are added to the EtherCAT chassis squeezer 3 for A+. Also, added are interfaces for the DC PD concentrator 9 and an additional auxiliary concentrator 1.

Change 6: EtherCAT Squeezer 3

Drawing: D1600509-v4 Wiring diagram: E1600386-v4 Work: Add controls for an AM modulated AOM amplifiers to the middle rail Add a new right rail for another AM modulated AOM amplifiers, and the two new concentrators. Needed by A+ upgrade for the middle rail: 1x D1700036-v2 1x D0902569-v1 1x Omron S82S-7305 1x EL9410 1x EL3104 1x EL4134 1x EL4134 1x EL1124 4x EL2124 *CALIFORNIA INSTITUTE OF TECHNOLOGY*



Needed by A+ upgrade for the right rail: 3x D0902569-v1 3x Omron S82S-7305 1x EK1100 2x EL9410 4x EL3104 1x EL3102 2x EL4134 2x EL1124 8x EL2124

A new EtherCAT chassis squeezer 4 is needed for the additional controls of the filter cavity.

Change 7: EtherCAT Squeezer 4

Drawing: D2000504-v1 Wiring diagram: E2100047-v1 Work: Install new chassis Maye require additional +24V power supply.

CALIFORNIA INSTITUTE OF TECHNOLOGY

E2000499-v3



Change 8: EtherCAT Squeezer 6

Drawing: D1300745-v6 Wiring diagram: E1300689-v8 Work: Add controls for the 3.125 MHz squeezer pickoff and the DCPD relays

Needed by A+ upgrade for the middle rail: 1x EL9410 (replace M9, reuse EL9190)

Needed by A+ upgrade for the right rail: 1x D1500088-v2 (rear panel) 1x D0902567-v1 (DB25M adapter) 1x D0902569-v1 (DB37M adapter) 1x Omron S82S-7305 1x EL9410 (replace R10, reuse EL9190) 1x EL3104 1x EL1124 2x EL2004

Change 9: EtherCAT Filter Cavity End

Drawing: D2200006-v1 Wiring diagram: E2200004-v1 Work: Install new chassis in filter cavity end station Requires installation of an EtherCAT media converter for single-mode fiber optic, CU1521-0010, in the MSR.

CALIFORNIA INSTITUTE OF TECHNOLOGY